



CY4/OL21D27N Flexible Rope Lay Copper Braid

By Burndy
Catalog # [CY4/OL21D27N](#)

Flexible Rope Lay Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number CY4/OL21D27N
UPC 621945470019

Dimensions

Dimension - L Length Overall	540.258 mm
mm	
Dimension - Length Overall	21.27 in
inch	
Length	21.27 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	6825

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50073260](#)
[Specifications - BURNDY_CY40L21D27N_Specsheet](#)
[Specifications - CY4/OL21D27N](#)