

## CY4/OL22G5TN Rope Lay Braid

By Burndy

Catalog # [CY4/OL22G5TN](#)

Tin Plated Ferrules.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	CY4/OL22G5TN
Connector Type	Braid
Material	Copper
UPC	781810668979
UPC 12 Digit	7818106689799

### Dimensions

Dimension - L Length Overall	559 mm
mm	
Dimension - Length Overall	22 in
inch	
Length	22 in
Weight	0.288 lb

### Electrical Ratings

Amperage Rating	335 A
-----------------	-------

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	UI
Status	

### Logistics

Minimum Pack Quantity	40
-----------------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50041108](#)  
[Specifications - CY4/OL22G5TN](#)  
[Specifications - BURNDY\\_CY40L22G5TN\\_Specsheet](#)