

CY541L10D88G1TN Rope Lay Braid

By Burndy

Catalog # [CY541L10D88G1TN](#)

Rope Lay Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	CY541L10D88G1TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	13
Plated	Y
UPC	781810363980
UPC 12 Digit	7818103639800

Dimensions

Dimension - L Length Overall	276 mm
mm	
Dimension - Length Overall	10.88 in
inch	
Length	10.88 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - CY541L10D88G1TN_MODEL-IGES](#)
- [3D Models - CY541L10D88G1TN_MODEL-STEP](#)
- [3D Models - CY541L10D88G1TN_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CYL_Lineart](#)
- [Sales Drawings - 10040450-01_A](#)
- [Specifications - CY541L10D88G1TN](#)