



CY6CL36G31 Flexible Rope Lay Copper Braid

By Burndy
Catalog # [CY6CL36G31](#)

Flexible Rope Lay Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number CY6CL36G31
UPC 621945469846

Dimensions

Dimension - L Length Overall 930 mm
mm
Dimension - Length Overall 36.6 in
inch
Length 36 in

Certifications And Compliance

Certification - CSA Approved No

Logistics

Carton Quantity 100
Minimum Pack Quantity 100
Pallet Quantity 3500

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50073104](#)
[Specifications - CY6CL36G31](#)