

# DUW31, Deadend Clamp, Copper Alloy

By Burndy  
Catalog # DUW31



High strength corrosion resistant copper alloy strain clamp with three DURUM U-bolts and single serrated saddle; Galvanized steel clevis pin; For Copper Conductors; RoHS Compatible; Material: Copper; Finish: Bright Dipped; Conductor Range (Main/Primary): 4/0 Str - 350 KCMIL.

## Features

- High strength, corrosion resistant copper alloy strain clamp
- Three silicon bronze U-bolts
- Single serrated saddle
- Galvanized steel clevis pin

## General

Catalog Number	DUW31
Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810013434

## Dimensions

Dimension - B Length fraction	4-14/25 in
Dimension - B Length inch	4.56 in
Dimension - Height fraction	1-47/50 in
Dimension - Height inch	1.94 in
Dimension - Height mm	49.3 mm
Dimension - L Length Overall mm	249 mm
Dimension - Length Overall inch	9.81 in
Dimension - Width fraction	2-11/25 in
Dimension - Width inch	2.44 in
Dimension - Width mm	62 mm

## Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil
Conductor - Copper Str Size Range	4/0 AWG-350 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	4
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Sales Drawings - SD..022054-01](#)
- [Specifications - DUW31](#)