

DUW44, Deadend Clamp, 500-1000 kcmil Copper

By Burndy
Catalog # [DUW44](#)



Cu Deadend clamp, 500-1000 kcmil.

Features

- High strength, corrosion resistant copper alloy strain clamp
- Three silicon bronze U-bolts
- Single serrated saddle
- Galvanized steel clevis pin

General

Catalog Number	DUW44
Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Bright Dipped
UPC	781810013458

Dimensions

Dimension - B Length fraction	5-1/4 in
Dimension - B Length inch	5.25 in
Dimension - Height fraction	2-64/79 in
Dimension - Height inch	2.81 in
Dimension - L Length Overall mm	290 mm
Dimension - Length Overall inch	11.43 in
Dimension - Width fraction	3-11/50 in
Dimension - Width inch	3.22 in
Dimension - Width mm	82 mm

Conductor Related

Conductor - Copper Str Size	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Size Range	500 kcmil-1000 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [3D Models - DUW44_MODEL-STEP](#)
- [3D Models - DUW44_MODEL-PDF](#)
- [3D Models - DUW44_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Ropes Course Industry Letter \(April 2021\)](#)
- [Product Cross Section Image\(s\) - BUR_DUW_LineArt](#)
- [Sales Drawings - SD..022054-01](#)
- [Specifications - DUW44](#)