

DUW46, Deadend Strain Clamp, 1000-1500 kcmil Copper

By Burndy
Catalog # [DUW46](#)



Cu Deadend Strain Clamp, 1000 - 1500 kcmil Cu.

General

Catalog Number	DUW46
Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Bright Dipped
UPC	781810013410

Dimensions

Dimension - B Length fraction	5-14/25 in
Dimension - B Length inch	5.56 in
Dimension - Height fraction	3-33/50 in
Dimension - Height inch	3.66 in
Dimension - Height mm	93 mm
Dimension - L Length Overall mm	294 mm
Dimension - Length Overall inch	11.59 in
Dimension - Width fraction	3-81/89 in
Dimension - Width inch	3.91 in
Dimension - Width mm	99 mm

Conductor Related

Conductor - Copper Str Size	1000 kcmil;1250 kcmil;1300 kcmil;1500 kcmil
Conductor - Copper Str Size Range	1000 kcmil-1500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Product Cross Section Image\(s\) - BUR_DUW_LineArt](#)
[Sales Drawings - SD..022054-01](#)
[Specifications - DUW46](#)