

DUW48, Deadend Clamp, Cast Copper Alloy

By Burndy
Catalog # [DUW48](#)



Cast Copper Alloy, Deadend Clamp, 1500 - 2000 kcmil, 4.14" Width.

General

Catalog Number	DUW48
Connector Type	Deadend
Material	Copper Alloy
Material - Hardware Plated	Galvanized Steel Y
Plating Type	Tin - Electro Plated
UPC	781810096956

Dimensions

Dimension - B Length fraction	5-14/25 in
Dimension - B Length inch	5.56 in
Dimension - Height fraction	3-18/25 in
Dimension - Height inch	3.72 in
Dimension - L Length Overall mm	294 mm
Dimension - Length Overall inch	11.59 in
Dimension - Width fraction	4-7/50 in
Dimension - Width inch	4.14 in
Dimension - Width mm	105 mm

Conductor Related

Conductor - Copper Str Size	1500 kcmil;1600 kcmil;1750 kcmil;2000 kcmil
Conductor - Copper Str Size Range	1500 kcmil-2000 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - SD..022054-01](#)
[Specifications - DUW48](#)