



EP 1 HP Series Electric/Hydraulic Pump, 220/230V-AC, Use with all 10,000 psi remote HYPRESS™ crimpers and cutters

By Burndy
Catalog # EP101HP2



Pump, EP 1 HP Series, 10K psi, 220/230V-AC.

Features

- Heavy duty design
- Roll cage
- Quick disconnect hydraulic coupler
- Oil level window
- 8 quart reservoir
- Factory set output pressure
- 1 HP motor dual voltage/hertz

Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EP101HP2
Power Source	1 HP 220/230V-AC; 50/60 Hz Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810033227
UPC 12 Digit	7818100332277

Dimensions

Dimensions	18.50 in x 11.75 in x 18.75 in
Height	18.75 in
Length	18.5 in
Weight	72 lb
Width	11.75 in

Electrical Ratings

Current Draw Max	10 Amperes
------------------	------------

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
Package Contents	Pump only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_082_OWFMF_EP10_lineart](#)
[Sales Drawings - SE..207894B](#)
[SDS - ALFLUID SDS](#)
[Specifications - EP101HP2](#)