



# EP 1/2 HP Series Electric/Hydraulic Pump, Use with all 10,000 psi remote HYPRESS™ crimpers and cutters

By Burndy  
Catalog # EP102



Pump, EP 1/2 HP Series, 10K psi.

## Features

- 1/2 HP motor
- Dual voltage/hertz
- Roll cage
- Quick disconnect hydraulic coupler
- Oil level window
- 8 quart reservoir
- Factory set output pressure

## Application

Pumping

## General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EP102
Power Source	1/2 HP 220/230V-AC; 50/60 Hz Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810033548
UPC 12 Digit	7818100335488

## Dimensions

Dimensions	18.50 in x 11.75 in x 17.5 in
Height	17.5 in
Length	18.5 in
Weight	68 lb
Width	11.75 in

## Electrical Ratings

Current Draw Max	10 Amperes
------------------	------------

## Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Pump only

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_EP10\\_LineArt](#)  
[Sales Drawings - SE..207894B](#)  
[SDS - ALFLUID SDS](#)  
[Specifications - EP102](#)