



# Electric Hydraulic Pump, 1/2 HP, Reservoir Volume 2 qts, 10000 psi, 115V AC/60Hz

By Burndy  
Catalog # [EPP10](#)

Pump, 10K psi, 1/2 HP, 115V AC/60Hz.



## Features

- Lightweight
- Small size
- Factory set relief valve
- 100,000 (+) life cycles
- Sealed electric pendant switch

## Application

Pumping

## General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
EU RoHS Indicator	Yes
Power Source	1/2 HP 115V-AC; 60 Cycle
Sub Brand	HYDRAULIC PUMP
Tool Type	Pump, Electric Hydraulic
Type	Pumps
UPC	781810033456
UPC 12 Digit	7818100334566

## Dimensions

Dimensions	16.00 in x 6.00 in x 8.00 in
Height	8 in
Length	16 in
Weight	30 lb
Width	6 in

## Electrical Ratings

Current Draw Max	12.5 Amperes
------------------	--------------

## Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Minimum Pack Quantity	1
Package Contents	Pump only

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Safety Operating & Maintenance Instructions EPP, EPP-EC Series](#)  
[Product Cross Section Image\(s\) - BUR\\_EPP10\\_LineArt](#)  
[Sales Drawings - SE207896-01](#)  
[SDS - ALFLUID SDS \(GHS\) \(2021-07\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-EPP10-SPEC-EN | REV 5/2024