



Electric/Hydraulic Pump Less Gage, 10,000 psi, 1/2 HP, 115V AC Motor

By Burndy
Catalog # [EPP10ECLG](#)

Pump Less Gage, 10K psi, 1/2 HP, 115V AC Motor.



Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EPP10ECLG
Power Source	1/2 HP 115V-AC Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810046623
UPC 12 Digit	7818100466233

Electrical Ratings

Current Draw Max	12.5 Amperes
------------------	--------------

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Pump only

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Safety Operating & Maintenance Instructions EPP, EPP-EC Series](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_EPP10ECLG_LineArt](#)
[Sales Drawings - SE209341-04](#)
[SDS - ALFLUID SDS](#)
[Specifications - EPP10ECLG](#)