



ES25A25A, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES25A25A](#)



Insulated AL service entrance compression sleeve for combinations of insulated CU, AL and ACSR conductors.

Application

For Insulated Combinations Of Copper, Aluminum, ACSR Compressed Conductors And In Overhead Distribution

General

Color Code - Side A	Yellow
Color Code - Side B	Yellow
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	INSULINK
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810013939
UPC 12 Digit	7818100139399

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - AL Str Size B Range	1/0 AWG
Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Str Size B	1/0
Conductor - Copper Str Size B Range	1/0

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	24000

Product Assets

[3D Models - ES25A25A_MODEL-IGES](#)
[3D Models - ES25A25A_MODEL-STEP](#)
[3D Models - ES25A25A_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_ES_Insulink_lineart](#)
[Sales Drawings - 50115706](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-ES25A25A-SPEC-EN | REV 5/2024

