



ES25R25RBOX, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES25R25RBOX](#)



1/0 - 1/0 ACSR.

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810191705
UPC 12 Digit	7818101917055

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	1/0 STR, 1 STR
Conductor - ACSR Str Size B	1/0 STR, 1 STR
Conductor - AL Str Size A	1/0 STR
Conductor - AL Str Size B	1/0 STR
Conductor - Copper Str Size A	1/0 STR
Conductor - Copper Str Size B	1/0 STR

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	24
Minimum Pack Quantity	1
Pallet Quantity	11136

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_ES_Insulink_lineart](#)
[Sales Drawings - sd040874-04](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-ES25R25RBOX-SPEC-EN | REV 5/2024