

ES25R25RG1, Service Entrance Sleeve Kit, contains 2 Insulated Sleeves, 1 Uninsulated Compression Sleeve

By Burndy
Catalog # [ES25R25RG1](#)



KIT CONTAINS:(2)ES25R25R & (1)YSU25R25R YELLOW:1/0 & 1 ACSR,1/0 & 1-19 STR CU/AL.

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

General

Catalog Number	ES25R25RG1
Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Type	Insulated Service Entrance Connectors
UPC	781810087794
UPC 12 Digit	7818100877944

Dimensions

Dimension - L Length Overall	70 mm
mm	

Dimension - Length Overall 2.75 in
inch

Dimension - Outside Diameter .75 in
inch

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	4500

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_ES_Insulink_lineart](#)
- [Sales Drawings - sd040874-04](#)
- [Specifications - ES25R25RG1](#)