

ES25R2RBOX, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES25R2RBOX](#)



ACSR: 1/0, #1 #2 AL/CU: 1/0, #1(19 STR) AL/CU #2, #1 INDEX: BG, 5/8" A(YELLOW) B(RED).

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

General

Catalog Number	ES25R2RBOX
Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810191712
UPC 12 Digit	7818101917122

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	1/0 STR, 1 STR
Conductor - ACSR Str Size B	2 AWG
Conductor - AL Str Size A	1/0 STR
Conductor - AL Str Size B	2 STR, 1 STR
Conductor - Copper Str Size A	1/0 STR
Conductor - Copper Str Size B	2 STR, 1 STR

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	24
Minimum Pack Quantity	1
Pallet Quantity	11136

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_ES_Insulink_lineart](#)
- [Sales Drawings - sd040874-03](#)
- [Specifications - ES25R2RBOX](#)