



ES2R2RBOX, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES2R2RBOX](#)



ACSR: #2, AL/CU: #2 STR - #1 STR AL/CU: #2 STR - #1 STR
INDEX: BG OR 5/8",RED-RED, Install with OH25, MD6.

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810191750
UPC 12 Digit	7818101917500

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	2 AWG
Conductor - ACSR Str Size B	2 AWG
Conductor - AL Str Size A	1 STR, 2 STR
Conductor - AL Str Size B	1 STR, 2 STR
Conductor - Copper Str Size A	1 STR, 2 STR
Conductor - Copper Str Size B	1 STR, 2 STR

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd040874-03](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-ES2R2RBOX-SPEC-EN | REV 1/2024