

ES2W8W, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES2W8W](#)



Insulated AL service entrance compression sleeve for combinations of insulated CU, AL and ACSR conductors, Color Code: Orange (Side A), Brown (Side B).

Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

General

Catalog Number	ES2W8W
Color	Brown
Color Code - Side A	Orange
Color Code - Side B	Brown
Construction Material - Main	Aluminum
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Sub Brand	INSULINK
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810142301
UPC 12 Digit	7818101423011

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size A Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A	4 AWG;3 AWG
Conductor - AL Str Size A Range	4 AWG-3 AWG
Conductor - AL Str Size B	8 AWG
Conductor - AL Str Size B Range	8 AWG
Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size A Range	2 AWG
Conductor - Copper Solid Size B	8 AWG
Conductor - Copper Solid Size B Range	8 AWG
Conductor - Copper Str Size A	4 AWG;3 AWG
Conductor - Copper Str Size A Range	4 AWG-3 AWG
Conductor - Copper Str Size B	10 AWG
Conductor - Copper Str Size B Range	10 AWG

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	24000

Product Assets

3D Models - ES2W8W_MODEL-STEP
3D Models - ES2W8W_MODEL-IGES
3D Models - ES2W8W_MODEL-PDF
Catalogs - BURNDY Master Catalog - Section H - Overhead
Distribution
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_ES_Insulink_lineart
Sales Drawings - 50115706
Specifications - ES2W8W



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-ES2W8W-SPEC-EN | REV 10/2024