

# ES4R4R, Insulated AL Service Entrance Compression Sleeve

By Burndy  
Catalog # ES4R4R



RUN/COURSE TAP/DERIVATION ACSR:6 S.B. 200% |6 S.B. 200% AL & CU:4 SOL-4 STR.|4 STR.-4 STR. COLOR/COULEUR: A-ORANGE, B-ORANGE.

## Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripsealed to limit oxidation and increase life of the connection

## General

Catalog Number	ES4R4R
Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810420423
UPC 12 Digit	7818104204233

## Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

## Conductor Related

Conductor - ACSR Str Size A	4 AWG
Conductor - ACSR Str Size B	4 AWG
Conductor - AL Str Size A	4 AWG
Conductor - AL Str Size B	4 AWG
Conductor - Copper Str Size A	4 AWG
Conductor - Copper Str Size B	4 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	24000

## Product Assets

- [3D Models - ES4R4R\\_MODEL-IGES](#)
- [3D Models - ES4R4R\\_MODEL-PDF](#)
- [3D Models - ES4R4R\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_ES\\_Insulink\\_lineart](#)
- [Sales Drawings - 50082742](#)
- [Specifications - ES4R4R](#)