

## FL1425X03D, Uninsulated Flag Style Female Quick Disconnect For 16 - 14 AWG (.25 x .03)

By Burndy  
Catalog # [FL1425X03D](#)



Uninsulated Flag Style Female Quick Disconnect For 16 - 14 AWG (.25 x .03).

### Features

- Flag-style female quick disconnects provide quick, reliable, snap-together interconnections without the use of tools
- Side entrance chamfer permits connections of 90° without bending the wire

### Application

Female Disconnect

### General

Catalog Number	FL1425X03D
Connector Type	Flag Female Quick Disconnect
EU RoHS Indicator	Yes
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810297346
UPC 12 Digit	7818102973466

### Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Length Overall inch	0.51 in
Dimension - Outside Diameter inch	0.15 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_Q18F18X02D\\_LineArt](#)  
[Sales Drawings - sd214278](#)  
[Specifications - FL1425X03D](#)