

# FL1825X03B, Uninsulated Flag Style Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy

Catalog # [FL1825X03B](#)



Uninsulated Flag Style Female Quick Disconnect For 22 - 18 AWG (.25 x .03).

## Features

- Flag-style female quick disconnects provide quick, reliable, snap-together interconnections without the use of tools
- Side entrance chamfer permits connections of 90° without bending the wire

## General

Catalog Number	FL1825X03B
Connector Type	Flag Female Quick Disconnect
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810327845
UPC 12 Digit	7818103278455

## Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Length Overall inch	0.50 in
Dimension - Outside Diameter inch	0.13 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

## Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
-----------------------------	---------------

Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd214278](#)
- [Specifications - FL1825X03B](#)