



FL1825X03D, Uninsulated Flag Style Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [FL1825X03D](#)



Uninsulated Flag Style Female Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Flag-style female quick disconnects provide quick, reliable, snap-together interconnections without the use of tools
- Side entrance chamfer permits connections of 90° without bending the wire

Application

Female Disconnect

General

Connector Type	Flag Female Quick Disconnect
EU RoHS Indicator	Yes
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810297339
UPC 12 Digit	7818102973399

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Length Overall inch	0.50 in
Dimension - Outside Diameter inch	0.13 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_Q18F18X02D_LineArt](#)
[Sales Drawings - sd214278](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-FL1825X03D-SPEC-EN | REV 5/2024