



FQP18F25X03D, Fully Insulated Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy
Catalog # [FQP18F25X03D](#)



Fully Insulated Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03).

Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

General

Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292952
UPC 12 Digit	7818102929522

Dimensions

Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - Industry Standards Met	UL310
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[3D Models - FQP18F25X03D_MODEL-PDF](#)
[3D Models - FQP18F25X03D_MODEL-STEP](#)
[3D Models - FQP18F25X03D_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094208](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-FQP18F25X03D-SPEC-EN | REV 5/2024