

## FT3B4/0, Power Distribution Block

By Burndy  
Catalog # FT3B4/0



Power Distribution Block, Max. 2 Wires per Phase, 3/0-4/0 AWG (Run), 6-4/0 AWG (Tap).

### General

Catalog Number	FT3B4/0
Connector Type	Power Distribution Block
Hex Size	1/4
Installation Torque	200 LBS/in
Recommended in-lb	
Material	Aluminum
Number Of Poles	3
Temperature Rating	194
Trade Name	U-BLOK™
UPC	781810113721
UPC 12 Digit	7818101137211

### Dimensions

Dimension - Height fraction	4-1/8
Dimension - Height inch	4.13 in
Dimension - Height mm	105 mm
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.88 in
Dimension - Width fraction	3-7/8 in
Dimension - Width inch	3.88 in
Dimension - Width mm	99 mm
Weight	1.25 lb

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Run	3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	3/0-4/0 AWG

Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	6-4/0 AWG
Conductor - Copper Str Run	3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	3/0-4/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	6-4/0 AWG
Number of Conductors	2

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_u-blok\\_la](#)  
[Sales Drawings - sd210528-01](#)  
[Specifications - BURNDY\\_FT3B40\\_Specsheet](#)  
[Specifications - FT3B4/0](#)