



FTU1, Power Distribution Block

By Burndy
Catalog # FTU1

Flexi U-Tap Assy, #2 - #1 AWG Cu/Al (Run), #12-#1 AWG Cu/Al (Tap).



General

Installation Torque Recommended in-lb	100 in-lb
Temperature Rating	194° F
Trade Name	FLEXITAP™
UPC	781810112588
UPC 12 Digit	7818101125888

Dimensions

Dimension - Height inch	1.44
Dimension - L Length Overall mm	19
Dimension - Length Overall inch	0.75
Dimension - Width mm	25 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run Range	1 AWG -2 AWG
Conductor - AL Str Tap Range	1 AWG - 12 AWG
Conductor - Copper Str Run Range	1 AWG -2 AWG
Conductor - Copper Str Tap Range	1 AWG - 12 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	7500
-----------------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SD210524](#)



A proud member of the Hubbell Family.