



FTU4/0, Power Distribution Block

By Burndy
Catalog # FTU4/0

BURNDY; Distribution Block; U-TAP; Flexitap; Conductor Size:
4/0 - 3/0 AWG Run; Tap Size: 6 - 4/0 AWG; Conductor Type:
Aluminum/Copper.



General

Installation Torque Recommended in-lb	200 in-lb
Temperature Rating	194° F
Trade Name	FLEXITAP™
UPC	781810113653
UPC 12 Digit	7818101136533

Dimensions

Dimension - Height inch	2
Dimension - L Length Overall mm	38
Dimension - Length Overall inch	1.5
Dimension - Width mm	32 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run Range	3/0 AWG - 4/0 AWG
Conductor - AL Str Tap Range	6 AWG -4/0 AWG
Conductor - Copper Str Run Range	3/0 AWG - 4/0 AWG
Conductor - Copper Str Tap Range	6 AWG -4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD210524](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-FTU4/0-SPEC-EN | REV 5/2024