

## GA25H26, Mechanical Ground Connector for Copper Cable to H-Beam

By Burndy  
Catalog # [GA25H26](#)



Mechanical Ground Connector for Copper Cable to "H" Beam;  
Accommodates: "H" Beam 1-7/8" - 2-1/2" x 2-1/2"; #4 Solid - 2/0 Stranded Copper

### Features

- High copper alloy ground connector
- Joins wide range of cable parallel to "H" beams or square tube
- Silicon bronze for superior corrosion protection

### Application

For Joining A Wide Range Of Copper Cable Parallel To H Beams Or Square Tube

### General

Catalog Number	GA25H26
EU RoHS Indicator	Yes
Installation Torque	240 Lb in
Recommended Run in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GA-H
UPC	781810001677
UPC 12 Digit	7818100016777

### Dimensions

Dimension - Height fraction	4-3/4 in
Dimension - Height inch	4.75 in
Dimension - Width inch	4.00 in
Dimension - Width mm	102 mm

### Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	6
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_gahla](#)  
[Sales Drawings - SC29935-01\\_2](#)  
[Specifications - GA25H26](#)