



GA400H294CTN, Mechanical Ground Connector for Copper Cable to 4" Square Fence Post, Tin Plated

By Burndy

Catalog # [GA400H294CTN](#)

Mechanical Ground Connector for Copper Cable to 4" Square Fence Post; Accommodates: #6 Solid - #4 Stranded (small clamp); 1/0 Solid - 4/0 Stranded (large clamp).

General

Catalog Number	GA400H294CTN
Installation Torque	150 Lb in
Recommended Run in-lb Plated	Y
Plating Type	Tin Plated
UPC	621945462328

Dimensions

Dimension - Height fraction	6-3/4 in
Dimension - Height inch	6.75 in
Dimension - Width inch	6.06 in
Dimension - Width mm	154 mm

Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	6 Sol. - 4 Str. (Small Run)-1/0 Sol. - 4/0 Str. (Large Run)



Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50068576](#)
[Specifications - GA400H294CTN](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-GA400H294CTN-SPEC-EN | REV 3/2025