



GAR1426SE, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1426SE](#)



To Rod or Pipe with the Same Connector.

General

Catalog Number	GAR1426SE
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	249
UPC	781810117194
UPC 14 Digit GTIN	00781810117194

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	3.00 in
Dimension - Height mm	76.2 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	1.05 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;0;2/0;3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	5;4;3;2;1;0;2/0
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	1/2;3/4

Conductor - Copper Tube Std Size Range	1/2-3/4
Conductor - Rebar Size	7;8
Conductor - Rebar Size Range	7-8
Conductor - Rod Size	7/8;1
Conductor - Rod Size Range	7/8-1
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD015789](#)
- [Specifications - GAR1426SE](#)



A Hubbell brand