



GAR1434, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1434](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 300 - 500 kcmil, #7 - #8 Rebar, 7/8" to 1" Rod, 1/2" - 3/4" Pipe, Bright Dipped.

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post

General

EU RoHS Indicator	Yes
Installation Torque	480 Lb in
Recommended Run in-lb	
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	247
UPC	781810232200
UPC 12 Digit	7818102322000

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Height fraction	3-3/4 in
Dimension - Height inch	3.75 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Outside Diameter inch	1.05 in
Dimension - Width fraction	2-3/4 in
Dimension - Width inch	2.75 in
Dimension - Width mm	70 mm

Conductor Related

Conductor - Copper Solid Size	300 Kcmil
Conductor - Copper Str Size	500 Kcmil
Conductor - Copper Str Size Range	300 kcmil - 500 kcmil
Conductor - Copper Tube Std Size	1/2 IPS IPS;3/4 IPS IPS
Conductor - Copper Tube Std Size Range	1/2 IPS IPS-3/4 IPS IPS
Conductor - Pipe or Round Tube Size Range	1/2-3/4 in
Conductor - Rebar Size	7 ;8
Conductor - Rebar Size Range	7 -8
Conductor - Rod Size	1 in
Conductor - Rod Size Range	7/8 in-1 in
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - GAR1434_MODEL-IGES](#)
[3D Models - GAR1434_MODEL-STEP](#)
[3D Models - GAR1434_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_GAR_Lineart](#)
[Sales Drawings - SD..015789-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GAR1434-SPEC-EN | REV 5/2024