



GAR1526SE, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1526SE](#)



To Rod or Pipe with the Same Connector.

General

Catalog Number	GAR1526SE
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	244
UPC	781810222621
UPC 12 Digit	7818102226211

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Width inch	2.62 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	5;4;3;2;1;1/0
Conductor - Copper Str Size Range	5 AWG - 1/0 AWG
Conductor - Copper Tube Std Size	1
Conductor - Copper Tube Std Size Range	1
Conductor - Rebar Size	9;10
Conductor - Rebar Size Range	9-10
Conductor - Rod Size	1 1/8;1 1/4
Conductor - Rod Size Range	1 1/8-1 1/4
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD015789](#)
[Specifications - GAR1526SE](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-GAR1526SE-SPEC-EN | REV 8/2024