



GAR1528CG4, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1528CG4](#)



To Rod or Pipe with the Same Connector.

General

Installation Torque Recommended Run in-lb	480 Lb in
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper
Material - Hardware Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin plated
U Bolt Type	311
UPC	621945012004
UPC 12 Digit	6219450120044

Dimensions

Dimension - B Length inch	1.12 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.12 in
Dimension - Outside Diameter inch	1.32 in
Dimension - Width inch	3 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - AL Str Size	2/0-4/0 AWG
Conductor - Copper Solid Size	4/0
Conductor - Copper Solid Size Range	4/0
Conductor - Copper Str Size	2/0-4/0 AWG
Conductor - Copper Str Size Range	2/0 AWG - 4/0 AWG
Conductor - Copper Tube Std Size	1
Conductor - Copper Tube Std Size Range	1
Conductor - Pipe or Round Tube Size Range	1 in
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50061774](#)



A proud member of the Hubbell Family.

