



## GAR1626G1TN, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy  
Catalog # [GAR1626G1TN](#)



Accommodates: #4 SOL - 2/0 STR Copper; 1-1/4" IPS; 1-3/8 to 1-1/2" Rod; Tin Plated; Direct Burial.

### Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

### General

Catalog Number	GAR1626G1TN
Installation Torque	240 Lb in
Recommended Run in-lb	
Material	Copper
Plated	Y
Plating Type	Tin plated
UPC	781810541234
UPC 12 Digit	7818105412344

### Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Pipe or Round	1-1/4 in
Tube Size Range	
Conductor - Rod Size	1.380-1.66 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [3D Models - GAR1626G1TN\\_MODEL-PDF](#)
- [3D Models - GAR1626G1TN\\_MODEL-IGES](#)
- [3D Models - GAR1626G1TN\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30024416](#)
- [Specifications - GAR1626G1TN](#)



A Hubbell brand