



GAR1728CG2, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR1728CG2](#)



To Rod or Pipe with the Same Connector.

General

Installation Torque	480 Lb in
Recommended Run in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
UPC	621945113008
UPC 12 Digit	6219451130088

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Pipe or Round Tube Size Range	1-1/2 in
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50061876](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GAR1728CG2-SPEC-EN | REV 5/2024