

# GAR1826SE, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy  
Catalog # [GAR1826SE](#)



To Rod or Pipe with the Same Connector.

## Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

## General

Catalog Number	GAR1826SE
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
U Bolt Type	257
UPC	781810117149
UPC 12 Digit	7818101171499

## Dimensions

Dimension - B Length inch	2.75 in
Dimension - Height inch	4.25 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

## Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	5;4;3;2;1;1/0
Conductor - Copper Str Size Range	5 AWG - 1/0 AWG
Conductor - Copper Tube Std Size	2
Conductor - Copper Tube Std Size Range	2
Conductor - Rod Size	2;2 1/4
Conductor - Rod Size Range	2-2 1/4
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> <li>• CU Tube Std-Size</li> <li>• Rod-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)

