



GAR1829G1TN, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GAR1829G1TN](#)



Ground Clamp Copper Tin plated 2/0 AWG-250 Kcmil
Installation Torque Recommended Run in-lb240 LB in.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

General

Catalog Number	GAR1829G1TN
Installation Torque	240 Lb-in
Recommended Run in-lb	
Material	Copper
Plated	Y
Plating Type	Tin plated
UPC	781810541210
UPC 12 Digit	7818105412100

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Str Size	250 Kcmil
Conductor - Pipe or Round	2 in
Tube Size Range	
Conductor - Rod Size	2 in-2.38 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GAR1829G1TN_MODEL-PDF](#)
- [3D Models - GAR1829G1TN_MODEL-IGES](#)
- [3D Models - GAR1829G1TN_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30024416](#)
- [Specifications - GAR1829G1TN](#)



A Hubbell brand