



# GAR184CW, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy  
Catalog # [GAR184CW](#)



Ground Clamp Copper Tin Plated bodies and electro tin plated hardware 8 AWG-4 AWG Installation Torque Recommended Run in-lb240 LB in.

## General

Installation Torque Recommended Run in-lb	240 Lb-in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin Plated bodies and electro tin plated hardware
U Bolt Type	257
UPC	781810116661
UPC 12 Digit	7818101166611

## Dimensions

Dimension - B Length inch	2.75 in
Dimension - Height inch	4.25 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

## Conductor Related

Conductor - Copper Solid Size	8 AWG
Conductor - Copper Solid Size Range	8-3
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Tube Std Size	2
Conductor - Copper Tube Std Size Range	2
Conductor - Pipe or Round Tube Size Range	2 in
Conductor - Rod Size	2 in-2.38 in
Conductor - Rod Size Range	2-2 1/4
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li><li>• CU Tube Std-Size</li><li>• Rod-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_GAR\\_Lineart](#)  
[Sales Drawings - SD015789](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GAR184CW-SPEC-EN | REV 5/2024