



# GAR204CW, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy  
Catalog # [GAR204CW](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG (Sol.) - 4 AWG (Str.), 3" to 3-1/2" Rod, 3" Pipe, Tin Plated.

## General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze Y
Plating Type	Tin - Hot Dipped
U Bolt Type	267
UPC	781810116630
UPC 12 Digit	7818101166300

## Dimensions

Dimension - B Length inch	3.50 in
Dimension - Height inch	5.63 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Outside Diameter inch	3.50 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

## Conductor Related

Conductor - Copper Solid Size	8;7;6;5;4;3
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	9;8;7;6;5;4
Conductor - Copper Str Size Range	9 AWG - 4 AWG
Conductor - Copper Tube Std Size	3;3 1/2
Conductor - Copper Tube Std Size Range	3-3 1/2
Conductor - Pipe or Round Tube Size	3 in
Conductor - Rod Size	3 - 3.5 in
Conductor - Rod Size Range	3
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li><li>• CU Tube Std-Size</li><li>• Rod-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_GAR\\_Lineart](#)  
[Sales Drawings - SD015789](#)



A proud member of the Hubbell Family.

BRDY-GAR204CW-SPEC-EN | REV 5/2024