



GAR214CW, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy
Catalog # [GAR214CW](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG -4 AWG, 3-1/2" Pipe, 3-1/2"-4" Rod, Hot Tin Dipped.

General

Installation Torque Recommended in-lb	240 LBS/in
Plating Type	Tin - Hot Dipped
U Bolt Type	264
UPC	781810051511

Dimensions

Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Outside Diameter inch	4.00 in
Dimension - Width fraction	5-3/8 in
Dimension - Width inch	5.31 in
Dimension - Width mm	135 mm

Conductor Related

Conductor - Copper Solid Size	8;7;6;5;4;3
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	9;8;7;6;5;4
Conductor - Copper Str Size Range	9-4
Conductor - Copper Tube Std Size	3 1/2;4
Conductor - Copper Tube Std Size Range	3 1/2-4
Conductor - Pipe or Round Tube Size	3 1/2 in
Conductor - Rod Size	3.5 - 4.0 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD015789](#)



A proud member of the Hubbell Family.