

GAR2226LD, Mechanical Grounding Connector, Cable to Rod or Pipe, Lead Plated

By Burndy
Catalog # [GAR2226LD](#)



Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 4" Pipe, 4"-4-1/2" Rod, Lead Plated.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

General

Catalog Number	GAR2226LD
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze Y
Plating Type	Lead
U Bolt Type	261
UPC	781810171332
UPC 12 Digit	7818101713322

Dimensions

Dimension - B Length inch	4.50 in
Dimension - Height inch	6.38 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	4.50 in
Dimension - Width fraction	5-7/8 in
Dimension - Width inch	5.81 in
Dimension - Width mm	148 mm

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	4;4 1/2
Conductor - Copper Tube Std Size Range	4-4 1/2
Conductor - Pipe or Round Tube Size	4 in
Conductor - Rod Size	4.0 - 4.5 in
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_GAR_Lineart](#)
[Sales Drawings - SD015789](#)



A proud member of the Hubbell Family.