



GAR3904BUW, Mechanical Grounding Connector, Conductor to Water Pipe, Tin Plated

By Burndy
Catalog # [GAR3903BUW](#)



#4 - 4/0 AWG; 1-1/4" to 2" Pipe; 3/8" Stud; Tin Plated; UL/CSA;
Rated for Direct Burial.

General

| | |
|---------------------------------------|---|
| Installation Torque Recommended in-lb | 200 LBS/in |
| Material | Bronze, Silicon (DURIUM is a trademark) |
| Material - Hardware Plated | Copper Alloy N |
| Plating Type | Unplated |
| UPC | 781810569894 |
| UPC 12 Digit | 7818105698944 |

Conductor Related

| | |
|-------------------------------------|-----------------|
| Conductor - Copper Solid Size Range | 4 AWG - 4/0 AWG |
| Conductor - Pipe or Round Tube Size | 1.25 - 2 in |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - UL Listed Direct Burial | Yes |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd206396](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GAR3903BUW-SPEC-EN | REV 1/2024