



GAR3906BUTN, Mechanical Grounding Connector, Tin Plated

By Burndy
Catalog # [GAR3906BUTN](#)



ACTUAL O.D.: 6.62 in. [168] 4 Str (.232) - 4/0 Str (.528) AWG
25mm² Str [6.6] - 95mm² str [12.0] TQ: 200 lb-in [22.5 Nm] Tin Plated.

Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

General

Catalog Number	GAR3906BUTN
Installation Torque	200 lb-in
Recommended in-lb	
Material	Copper Alloy
Plated	N
Plating Type	Tin Electro Plated
UPC	781810501115
UPC 12 Digit	7818105011155

Dimensions

Dimension - Height inch	8.50 in
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	6.62 in

Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Pipe or Round Tube Size	6 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

Product Assets

- [3D Models - GAR3906BUTN_MODEL-PDF](#)
- [3D Models - GAR3906BUTN_MODEL-IGES](#)
- [3D Models - GAR3906BUTN_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GARBU_Lineart](#)
- [Sales Drawings - sd206396](#)
- [Specifications - GAR3906BUTN](#)