



GAR3906TC, Mechanical Ground Connector, For 2 Hole Lug to Pipe or Rod

By Burndy
Catalog # [GAR3906TC](#)



Water Pipe Ground Connector, 6" Rod, Large, smooth connector contact area between pipe and ground clamp

Application

For Direct Burial, Water Pipe As Well As Structural And Reinforcing Rod Shapes

General

EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	240 lb-in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	3
Physical Attribute - Pad Configuration	2.50 x 2.50 - 3 Holes
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	Rod or Tube Clamp with Mounting Pad
U Bolt Type	1027
UPC	781810001592
UPC 12 Digit	7818100015922

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Height inch	8.50 in
Dimension - Length Overall inch	2.50 in
Dimension - Outside Diameter inch	6.62 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16
Dimension - Width inch	9.12 in
Dimension - Width mm	232 mm

Conductor Related

Conductor - Copper Tube EH Size	6
Conductor - Copper Tube EH Size Range	6
Conductor - Pipe or Round Tube Size	6 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - se..206158-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GAR3906TC-SPEC-EN | REV 1/2024