



GAR3908BU, Mechanical Grounding Connector, Conductor to Water Pipe

By Burndy
Catalog # [GAR3908BU](#)

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 10" Pipe, 3/8" Stud, W/ silicon bronze hardware.



Application

For Connecting A Small To Medium Range Copper Ground Conductor To Water Pipe As Well As Structural And Reinforcing Rod Shapes

General

EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	200 lb-in
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GAR-BU
U Bolt Type	1029
UPC	781810001554
UPC 12 Digit	7818100015544

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	12.00 in
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	10.75 in
Dimension - Width inch	12.75 in
Dimension - Width mm	324 mm

Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size	4;3;2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Size Range	4 AWG - 4/0 AWG
Conductor - Copper Tube Std Size	10
Conductor - Copper Tube Std Size Range	10
Conductor - Pipe or Round Tube Size	10 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd206396](#)



A proud member of the Hubbell Family.