



## GAR3909BU, Mechanical Grounding Connector, Conductor to Water Pipe

By Burndy  
Catalog # [GAR3909BU](#)



Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 12" Pipe, 3/8" Stud, W/ silicon bronze hardware.

### Features

- Cable clamp swivels at 90°
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

### General

Catalog Number	GAR3909BU
Installation Torque	200 lb-in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	1030
UPC	781810001561
UPC 12 Digit	7818100015611

### Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	14.00 in
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	12.75 in
Dimension - Width inch	14.75 in
Dimension - Width mm	375 mm

### Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size	4;3;2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Size Range	4 AWG - 4/0 AWG
Conductor - Copper Tube Std Size	12
Conductor - Copper Tube Std Size Range	12
Conductor - Pipe or Round Tube Size	12 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_GARBU\\_Lineart](#)  
[Sales Drawings - sd206396](#)  
[Specifications - GAR3909BU](#)



A Hubbell brand