



GAR3909TC, Mechanical Ground Connector, For 2 Hole Lug to Pipe or Rod

By Burndy
Catalog # [GAR3909TC](#)



Mechanical Ground Connector, For 2 Hole Lug to Water Pipe or Rod, 12" IPS, 3/8" Bolt.

Features

- Large, smooth connector contact area between pipe and ground clamp to maximize contact area between connector and pipe
- Pre-drilled pad for 2-3/8" bolts on 1" centers to allow for direct mounting of 2-hole compression terminals up to 750 kcmil to pipe
- One-wrench installation
- UL467 Listed for the US and Canadian Markets

General

Catalog Number	GAR3909TC
Installation Torque	240 lb-in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	3
Physical Attribute - Pad Configuration	3.63 x 2.67 - 3 Holes
Plated	N
Plating Type	Unplated
Type	Rod or Tube Clamp with Mounting Pad
U Bolt Type	1030
UPC	781810001622
UPC 14 Digit GTIN	00781810001622

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Height inch	14.00
Dimension - Height mm	355.6
Dimension - Length Overall inch	3.63
Dimension - Outside Diameter inch	12.75
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Dimension - Width inch	15.25
Dimension - Width mm	387

Conductor Related

Conductor - Copper Tube EH Size	12
Conductor - Pipe or Round Tube Size	12 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GAR3900_Lineart](#)
[Sales Drawings - SE206158-02_2](#)
[Specifications - GAR3909TC](#)