



# GAR396925BU, Mechanical Grounding Connector, Conductor to Water Pipe

By Burndy  
Catalog # [GAR396925BU](#)



Mechanical Grounding Connector - Conductor to Water Pipe, #8 - 1/0 AWG; 2-1/2" Pipe; UL/CSA; Rated for Direct Burial.

## General

Installation Torque Recommended in-lb	200 lb-in
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Plating Type	Unplated
UPC	781810421970
UPC 12 Digit	7818104219700

## Dimensions

Dimension - Height inch	4.00 in
Dimension - Width inch	4.50 in
Dimension - Width mm	114 mm

## Conductor Related

Conductor - Copper Solid Size Range	#8 AWG - 1/0 AWG
Conductor - Copper Str Size Range	8;7;6;5;4;3;2;1;1/0
Conductor - Copper Tube Std Size	2 1/2
Conductor - Copper Tube Std Size Range	2 1/2
Conductor - Pipe or Round Tube Size	2.50 in

## Certifications and Compliance

Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - CSKCO33823](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GAR396925BU-SPEC-EN | REV 1/2024