



# GB26OSBHEXCTW, Mechanical Grounding Connector, Cable to Bar

By Burndy  
Catalog # [GB26OSBHEXCTW](#)



Mechanical Grounding Connector, 4 AWG (Sol)-2/0 AWG (Str), 3/8" Stud.

## General

Installation Torque Recommended in-lb	240 lb-in
Material	Copper Alloy
Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Plating Type	Tin Plated
UPC	781810079454
UPC 12 Digit	7818100794544

## Dimensions

Dimension - Height inch	2.02 in
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	0.94 in
Dimension - Width fraction	1-1/2 in
Dimension - Width inch	1.52 in

## Conductor Related

Conductor - Copper Solid Size Range	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size Range	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	12
-----------------------	----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50080158](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-GB26OSBHEXCTW-SPEC-EN | REV 5/2024