



GB26T4GSTN, Mechanical Grounding Connector, Cable to Bar, Galvanized Steel, Tin Plated

By Burndy
Catalog # [GB26T4GSTN](#)



Mechanical Grounding Connector, Cable to 1/2" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), Hardware: Galvanized Steel, Tin Plated.

General

Installation Torque Recommended in-lb	240 lb-in
Plating Type	Tin Plated
UPC	621945461635

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Height inch	2.18 in
Dimension - Length Overall inch	0.94 in
Dimension - Width fraction	1-5/9 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - Copper Solid Size Range 4 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sc091657-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GB26T4GSTN-SPEC-EN | REV 1/2024