



GB29G69HEXW, Mechanical Grounding Connector, Cable to Bar, Tin Plated

By Burndy
Catalog # [GB29G69HEXW](#)



Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 2/0 AWG (Sol) -250 kcmil, 1/2" Stud, 1.5 IN Width. Hot Tin Dipped.

General

Catalog Number	GB29G69HEXW
Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Tin - Hot Dipped
UPC	781810167236
UPC 12 Digit	7818101672366

Dimensions

Dimension - Height inch	1.75 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Width fraction	1-24/25 in
Dimension - Width inch	1.96 in

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10020194](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-GB29G69HEXW-SPEC-EN | REV 6/2024